

- The Cement Flow Table according to EN standard. Used for determining the consistency of mortar, lime and cement specimens. Also manual and motorized models are available.
- The hand operated model is fitted with a hand wheel. The motor operated model is driven by a motor speed reducer through a mechanical coupling at the rate of 1 revolution per second. The number of drops is preset on a counter and the machine stops automatically at the end of the cycle.
- EN model, the table is manufactured from steel, stainless steel or brass and has a 300 mm diameter table. The conical mould is made of brass or steel and has dimensions of 100 mm base dia. x 70 mm top dia. x 60 mm height.



#### Technical Parameter:

1. Total Weight of pulsatory Part: 4.35Kg 0.15Kg
2. Drop height: 10mm+0.2mm
3. Diameter of table: 300mm 1mm
4. Flow mould: 70mm and 100mm diameter X 60mm deep.
5. Tamper: 20mm diameter, 200mm long;

**CST Instruments (Thailand) Co., Ltd.**

Tel : 086-086-2000 / 02-915-1693

Tax ID : 0105566170152

95 Rom Klao Road, Khlong Sam Prawet, Lat Krabang, Bangkok 10520